Product data sheet

Specifications





graphic display terminal, Altivar, 240 x 160pixels, IP65

VW3A1111

Product availability: Stock - Normally stocked in distribution facility

Price*: 210.00 USD

Main

Range Of Product	Altivar
Range Compatibility	Altivar Process ATV900
	Altivar Process ATV600
	Altivar Machine ATV340
Accessory / Separate Part Category	Display and signalling accessories
Accessory / Separate Part Type	Display terminal
Accessory / Separate Part Destination	Variable speed drive
Product Specific Application	To control, adjust and configure the drive
	To save and download configurations
	To display the current values
Ip Degree Of Protection	IP65

Complementary

Language	Spanish
	Romanian
	Turkish
	Polish
	Swedish
	Estonian
	Bulgarian
	English
	Russian
	Greek
	Danish
	Hungarian
	Chinese
	Norwegian
	Lituanien
	French
	Brazilian
	German
	Korean
	Portuguese
	Finnish
	Czech
	Slovak
	Taiwanese
	Dutch
	Italian
	Ukrainian
Realtime Clock	Built-in
Battery Size	CR2032
Battery Life	10 year(s)
Display Type	Backlit LCD screen white and red
Messages Display Capacity	8 lines

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Pixel Resolution	240 x 160
Net Weight	0.44 lb(US) (0.2 kg)

Environment

Ambient Air Temperature For	5122 °F (-1550 °C)
Operation	

Ordering and shipping details

Category	US1CP4E22205
Discount Schedule	CP4E
Gtin	3606480702235
Returnability	Yes
Country Of Origin	ID

Packing Units

•		
Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	
Package 1 Height	2.24 in (5.7 cm)	
Package 1 Width	5.39 in (13.7 cm)	
Package 1 Length	7.32 in (18.6 cm)	
Package 1 Weight	9.31 oz (264.0 g)	
Unit Type Of Package 2	S03	
Number Of Units In Package 2	20	
Package 2 Height	11.81 in (30.0 cm)	
Package 2 Width	11.81 in (30.0 cm)	
Package 2 Length	15.75 in (40.0 cm)	
Package 2 Weight	13.38 lb(US) (6.069 kg)	
Unit Type Of Package 3	P06	
Number Of Units In Package 3	80	
Package 3 Height	17.72 in (45.0 cm)	
Package 3 Width	23.62 in (60.0 cm)	
Package 3 Length	31.50 in (80.0 cm)	
Package 3 Weight	72.26 lb(US) (32.776 kg)	

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free
Rohs Exemption Information Yes
Pvc Free

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov