Product data sheet

Specification





additional output module, Altivar, relay output, 24 to 30V DC, 1 screw terminal

VW3A3204

Product availability: Stock - Normally stocked in distribution facility

Price*: 234.00 USD

Main

Product Or Component Type	Additional output module
Range Compatibility	Altivar Machine ATV340 Easy Altivar 610
	Altivar Process ATV900
	Altivar Process ATV600
Input/Output Type	3 relay output
Discrete Output Number	3
Discrete Output Type	R4, R5, R6) relay normally open 1 ms

Complementary

Electrical Durability	100000 cycles	
Minimum Switching Current	5 mA 24 V DC	
Maximum Switching Current	2 A 250 V AC inductive, cos phi = 0.4 5 ms 2 A 30 V DC inductive, cos phi = 0.4 5 ms 5 A 250 V AC resistive, cos phi = 1 5 ms 5 A 30 V DC resistive, cos phi = 1 5 ms	
Electrical Connection	Screw terminal block, 1.5 mm² / AWG 16, 4.43 lbf.in (0.5 N.m)	
Net Weight	0.88 lb(US) (0.4 kg)	

Ordering and shipping details

Category	US1CP4E22207
Discount Schedule	CP4E
Gtin	3606480702532
Returnability	Yes
Country Of Origin	ID

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.56 in (6.5 cm)
Package 1 Width	5.12 in (13.0 cm)
Package 1 Length	7.48 in (19.0 cm)
Package 1 Weight	5.36 oz (152.0 g)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Unit Type Of Package 2	S03
Number Of Units In Package 2	16
Package 2 Height	11.81 in (30.0 cm)
Package 2 Width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	6.87 lb(US) (3.114 kg)



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov