Product data sheet

Specifications





Compact discovery packs, Zelio Logic, smart relay discovery pack, 20 I/O, 100...240 V AC

SR2PACK2FU

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 486.00 USD

Main

Range Of Product	Zelio Logic
Product Or Component Type	Compact discovery packs
Discrete Input Number	12
Number Of Outputs	8 relay

Complementary

Complementary	
Kit Composition	SR2B201FU Cable PC SR2USB01 for connection to PC
Input/Output Number	20
Local Display	With
Number Or Control Scheme Lines	120 ladder 0200 FBD
Cycle Time	690 ms
Backup Time	10 years 77 °F (25 °C)
Clock Drift	12 min/year 32131 °F (055 °C) 6 s/month 77 °F (25 °C)
Checks	Program memory on each power up
[Us] Rated Supply Voltage	100240 V
Supply Voltage Limits	85264 V
Supply Frequency	50/60 Hz
Maximum Supply Current	100 mA 100 V without extension) 50 mA 240 V without extension)
Power Consumption In Va	11 VA without extension
Isolation Voltage	1780 V
Protection Type	Against inversion of terminals (control instructions not executed)
Discrete Input Voltage	100240 V AC
Discrete Input Current	0.6 mA
Discrete Input Frequency	5763 Hz 4753 Hz
Voltage State 1 Guaranteed	>= 79 V discrete input
Voltage State 0 Guaranteed	<= 40 V discrete input
Current State 1 Guaranteed	>= 0.17 mA discrete input)

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Current State 0 Guaranteed	<= 0.5 mA discrete input)
Input Impedance	350 kOhm discrete input
Output Voltage Limits	530 V DC relay output) 24250 V AC
Contacts Type And Composition	NO relay output
Output Thermal Current	8 A for all 8 outputs relay output
Electrical Durability	AC-12 500000 cycles 230 V, 1.5 A relay output IEC 60947-5-1 AC-15 500000 cycles 230 V, 0.9 A relay output IEC 60947-5-1 DC-12 500000 cycles 24 V, 1.5 A relay output IEC 60947-5-1 DC-13 500000 cycles 24 V, 0.6 A relay output IEC 60947-5-1
Switching Capacity In Ma	>= 10 mA 12 V relay output)
Operating Rate In Hz	0.1 Hz at le)relay output 10 Hz no load)relay output
Mechanical Durability	1000000 cycles relay output
[Uimp] Rated Impulse Withstand Voltage	4 kV conforming to EN/IEC 60947-1 and EN/IEC 60664-1
Clock	Without
Response Time	50 ms ladder from state 0 to state 1)discrete input 50 ms ladder from state 1 to state 0)discrete input 50255 ms FBD from state 0 to state 1)discrete input 50255 ms FBD from state 1 to state 0)discrete input 10 ms from state 0 to state 1)relay output 5 ms from state 1 to state 0)relay output
Connections - Terminals	screw terminals, 1 x 0.21 x 2.5 mm ² AWG 25AWG 14) semi-solid screw terminals, 1 x 0.21 x 2.5 mm ² AWG 25AWG 14) solid screw terminals, 1 x 0.251 x 2.5 mm ² AWG 24AWG 14) flexible with cable end screw terminals, 2 x 0.22 x 1.5 mm ² AWG 24AWG 16) solid screw terminals, 2 x 0.252 x 0.75 mm ² AWG 24AWG 18) flexible with cable end
Tightening Torque	4.43 lbf.in (0.5 N.m)
Overvoltage Category	III IEC 60664-1
Net Weight	1.87 lb(US) (0.85 kg)

Environment

Immunity To Microbreaks	10 ms
Product Certifications	UL C-tick GL CSA GOST
Standards	IEC 61000-4-2 level 3 IEC 60068-2-27 Ea IEC 61000-4-5 IEC 61000-4-6 level 3 IEC 61000-4-3 IEC 60068-2-6 Fc IEC 61000-4-4 level 3 IEC 61000-4-12 IEC 61000-4-11
Ip Degree Of Protection	IP20 IEC 60529 terminal block) IP40 IEC 60529 front panel)
Environmental Characteristic	EMC directive IEC 61000-6-2 EMC directive IEC 61000-6-3 EMC directive IEC 61000-6-4 EMC directive IEC 61131-2 zone B Iow voltage directive IEC 61131-2
Disturbance Radiated/Conducted	Class B EN 55022-11 group 1
Pollution Degree	2 IEC 61131-2

Ambient Air Temperature For Operation	-4104 °F (-2040 °C) in non-ventilated enclosure IEC 60068-2-1 and IEC 60068-2-2 -4131 °F (-2055 °C) IEC 60068-2-1 and IEC 60068-2-2
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)
Operating Altitude	6561.68 ft (2000 m)
Maximum Altitude Transport	10000.00 ft (3048 m)
Relative Humidity	95 % without condensation or dripping water

Ordering and shipping details

Category	US1000l22378
Discount Schedule	0001
Gtin	3389110549744
Returnability	No
Country Of Origin	FR

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.44 in (6.2 cm)
Package 1 Width	6.02 in (15.3 cm)
Package 1 Length	9.13 in (23.2 cm)
Package 1 Weight	21.13 oz (599 g)
Unit Type Of Package 2	S03
Number Of Units In Package 2	10
Package 2 Height	11.81 in (30 cm)
Package 2 Width	11.81 in (30 cm)
Package 2 Length	15.75 in (40 cm)
Package 2 Weight	14.58 lb(US) (6.613 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free
Rohs Exemption Information Yes
Pvc Free

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov