

Product data sheet

Specifications



GSM modem interface, Zelio Logic, for communication interface SR2COM01

SR2MOD02

! Discontinued

! Discontinued on: Jun 20, 2023

! To be end-of-service on: Dec 31, 2024

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range Of Product	Zelio Logic
Product Or Component Type	GSM modem
Type Of Modem	Type quad band 900/1800 MHz, 850/1900 MHz
Data Backed Up	Flash memory

Complementary

Kit Composition	GSM modem Fixing on DIN rail (assembled with the GSM modem) 1 supply cable 1 antenna with cable 2 lugs for plate mounting
Function Available	Send alarm/receive instruction Send alarm to e-mail address Transfer program Update firmware monitoring
Number Of Messages	28
Electrical Data Recording	Telephone/e-mail Discrete and digital value Date and time
[Us] Rated Supply Voltage	12...24 V DC
Supply Voltage Limits	5.5...32 V
Maximum Supply Current	165 mA 12 V 87 A 24 V 2100 mA 5.5 V
Power Dissipation In W	2.1 W
Associated Fuse Rating	2.5 A
Electrical Connection	1 cable Com-M Com-M specific to Zelio RS232 serial, specific Zelio communication protocol link with the modem, AT commands 1 antenna with cable 1 cable 1 cable Com-Z Com-Z specific to Zelio, specific Zelio communication protocol Zelio Logic smart relays SR.B..... and SR2 E..... Version (>= V3.1) Supply cable
Cable Length	4.92 ft (1.5 m) supply cable 8.20 ft (2.5 m) antenna with cable
Insulation	1780 V optocoupler Com-Z specific to Zelio By the cable SR2 CBL07 Com-M specific to Zelio

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Connections - Terminals	Screw terminals, 1 x 0.25...1 x 2.5 mm² AWG 24...AWG 14) flexible with cable end Screw terminals, 2 x 0.25...2 x 0.75 mm² AWG 24...AWG 18) flexible with cable end Screw terminals, 1 x 0.25...1 x 2.5 mm² AWG 24...AWG 14) semi-solid Screw terminals, 1 x 0.25...1 x 2.5 mm² AWG 24...AWG 14) solid Screw terminals, 2 x 0.25...2 x 1.5 mm² AWG 23...AWG 16) solid
Tightening Torque	4.43 lbf.in (0.5 N.m)
Net Weight	0.74 lb(US) (0.335 kg)

Environment

Product Certifications	UL PTCRB GOST CSA IC FCC part 15 standard C-tick
Standards	EN/IEC 60068-2-6 Fc EN/IEC 60068-2-32
Electromagnetic Compatibility	Conducted and radiated emissions class B group 1 conforming to EN 55022-11
Ip Degree Of Protection	IP31 IEC 60529
Environmental Characteristic	Low voltage directive EN/IEC 60950-1 R and TTE directive ETSI EN 301419-1 R and TTE directive ETSI EN 301 489-7 R and TTE directive ETSI EN 301 511 EMC directive ETSI EN 301 489-1
Pollution Degree	2 EN/IEC 61131-2
Ambient Air Temperature For Operation	-4...131 °F (-20...55 °C) IEC 60068-2-2 -4...131 °F (-20...55 °C) IEC 60068-2-2
Ambient Air Temperature For Storage	-40...158 °F (-40...70 °C)
Operating Altitude	6561.68 ft (2000 m)
Maximum Altitude Transport	10000.00 ft (3048 m)
Relative Humidity	0...95 % 131 °F (55 °C) without condensation 0...95 % without condensation, during storage

Ordering and shipping details

Category	US1000I22378
Discount Schedule	000I
Gtin	3389119203999
Returnability	No
Country Of Origin	FR

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.95 in (7.5 cm)
Package 1 Width	2.95 in (7.5 cm)
Package 1 Length	5.79 in (14.7 cm)
Package 1 Weight	11.22 oz (318.0 g)
Unit Type Of Package 2	S03
Number Of Units In Package 2	20

Package 2 Height	11.81 in (30.0 cm)
Package 2 Width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	15.20 lb(US) (6.895 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability




Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)


Well-being performance

 Mercury Free	
 Rohs Exemption Information	Yes
 Pvc Free	
Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Dimensions Drawings

GSM Modem

Rail Mounting



Screw Fixing

