Product data sheet

Specification





discrete IO extension module, Zelio Logic SR2 SR3, 10 IO, 100 to 240V AC

SR3XT101FU

Product availability: Stock - Normally stocked in distribution

Price*: 126.00 USD

Main

Range Of Product	Zelio Logic
Product Or Component Type	Discrete I/O extension module

Complementary

Number Or Control Scheme Lines	120 ladder	
Cycle Time	690 ms	
Backup Time	10 years 77 °F (25 °C)	
Clock Drift	12 min/year 32131 °F (055 °C)	
Checks	Program memory on each power up	
[Us] Rated Supply Voltage	100240 V AC	
Supply Voltage Limits	85264 V	
Supply Frequency	50/60 Hz	
Reverse Polarity Protection	With	
Discrete Input Number	6	
Discrete Input Voltage	100240 V AC	
Discrete Input Current	0.6 mA	
Discrete Input Frequency	4753 Hz 5763 Hz	
Voltage State 1 Guaranteed	>= 79 V discrete input	
Voltage State 0 Guaranteed	<= 40 V discrete input	
Current State 1 Guaranteed	>= 0.17 mA discrete input)	
Current State 0 Guaranteed	<= 0.5 mA discrete input)	
Input Impedance	350 kOhm discrete input	
Number Of Outputs	4 relay	
Output Voltage Limits	530 V DC relay output) 24250 V AC	
Contacts Type And Composition	NO relay output	
Output Thermal Current	8 A for all 4 outputs relay output	
Electrical Durability	AC-15 500000 cycles 230 V, 0.9 A relay output IEC 60947-5-1 AC-12 500000 cycles 230 V, 1.5 A relay output IEC 60947-5-1 DC-13 500000 cycles 24 V, 0.6 A relay output IEC 60947-5-1 DC-12 500000 cycles 24 V, 1.5 A relay output IEC 60947-5-1	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Switching Capacity In Ma	>= 10 mA 12 V relay output)	
Operating Rate In Hz	0.1 Hz at le)relay output 10 Hz no load)relay output	
Mechanical Durability	10000000 cycles relay output	
[Uimp] Rated Impulse Withstand 4 kV EN/IEC 60947-1 and EN/IEC 60664-1 Voltage		
Response Time	50 ms ladder from state 0 to state 1)discrete input 50 ms ladder from state 1 to state 0)discrete input 50255 ms FBD from state 0 to state 1)discrete input 50255 ms FBD from state 1 to state 0)discrete input 10 ms from state 0 to state 1)relay output 5 ms from state 1 to state 0)relay output	
Connections - Terminals	Screw terminals, 1 x 0.251 x 2.5 mm² AWG 24AWG 14) flexible with cable end Screw terminals, 2 x 0.252 x 0.75 mm² AWG 24AWG 18) flexible with cable end Screw terminals, 1 x 0.21 x 2.5 mm² AWG 25AWG 14) semi-solid Screw terminals, 1 x 0.21 x 2.5 mm² AWG 25AWG 14) solid Screw terminals, 2 x 0.22 x 1.5 mm² AWG 24AWG 16) solid	
Tightening Torque	4.43 lbf.in (0.5 N.m)	
Overvoltage Category	oltage Category III IEC 60664-1	
Net Weight	eight 0.44 lb(US) (0.2 kg)	

Environment

Product Certifications	GOST
	UL
	CSA
	C-tick
	GL
	GL
Standards	IEC 60068-2-27 Ea
	IEC 61000-4-12
	IEC 61000-4-3
	IEC 61000-4-2 level 3
	IEC 61000-4-5
	IEC 61000-4-6 level 3
	IEC 60068-2-6 Fc
	IEC 61000-4-11
	IEC 61000-4-11
	IEC 61000-4-4 level 3
Ip Degree Of Protection	IP20 IEC 60529 terminal block)
	IP40 IEC 60529 front panel)
Environmental Characteristic	EMC directive IEC 61000-6-2
	EMC directive IEC 61000-6-3
	EMC directive IEC 61000-6-4
	EMC directive IEC 61131-2 zone B
	Low voltage directive IEC 61131-2
	Low voltage directive IEC 01131-2
Disturbance Radiated/Conducted	Class B EN 55022-11 group 1
Pollution Degree	2 IEC 61131-2
Ambient Air Temperature For	-4104 °F (-2040 °C) in non-ventilated enclosure IEC 60068-2-1 and IEC
Operation	60068-2-2
•	-4131 °F (-2055 °C) IEC 60068-2-1 and IEC 60068-2-2
	-4131 1 (-2033 0) IEO 00000-2-1 and IEO 00000-2-2
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)
Operating Altitude	6561.68 ft (2000 m)
Maximum Altitude Transport	10000.00 ft (3048 m)
Relative Humidity	95 % without condensation or dripping water

Ordering and shipping details

Category	US1000I22378
Discount Schedule	0001

Gtin	3389110550139
Returnability	Yes
Country Of Origin	FR

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.56 in (6.500 cm)
Package 1 Width	3.54 in (9.000 cm)
Package 1 Length	3.94 in (10.000 cm)
Package 1 Weight	6.46 oz (183.000 g)
Unit Type Of Package 2	S03
Number Of Units In Package 2	30
Package 2 Height	11.81 in (30.000 cm)
Package 2 Width	11.81 in (30.000 cm)
Package 2 Length	15.75 in (40.000 cm)
Package 2 Weight	13.15 lb(US) (5.967 kg)

Contractual warranty

Warranty 18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Mercury Free	
②	Rohs Exemption Information	Yes
	Pvc Free	

Certifications & Standards


Reach Regulation	REACh Declaration	
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)	
China Rohs Regulation	China RoHS declaration	
Environmental Disclosure	Product Environmental Profile	
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.	
Circularity Profile	End of Life Information	

SR3XT101FU


Dimensions Drawings

I/O Extension Modules

Mounting on 35 mm/1.38 in. DIN Rail



Screw Fixing (Retractable Lugs)




SR3	a (mm/in.)	G (mm/in.)
XT61••	35 / 1.38	25 / 0.98
XT101••	72 / 2.83	60 / 2.36
XT141••	72 / 2.83	60 / 2.36

Connections and Schema

Connection of Smart Relays on AC Supply


SR••••1B, SR••••1FU



- (1) 1 A quick-blow fuse or circuit-breaker.
- (2) Fuse or circuit-breaker.
- (3) Inductive load.
- (4) Q9 and QA: 5 A (max. current in terminal C: 10 A).

With Discrete I/O Extension Module

SR3B•••B + SR3XT•••B, SR3B•••FU + SR3XT•••FU



(1) 1 A quick-blow fuse or circuit-breaker.

NOTE: QF and QG: 5 A for SR3XT141..


SR3XT101FU

Performance Curves

Compact and Modular Smart Relays

Electrical Durability of Relay Outputs


(in millions of operating cycles, conforming to IEC/EN 60947-5-1) AC-12 (1)



X: Current (A)

Y: Millions of operating cycles


(1) AC-12: switching resistive loads and opto-coupler isolated solid-state loads, $\cos \ge 0.9$. AC-14 (1)



X: Current (A)

Y: Millions of operating cycles

(1) AC-14: switching small electromagnetic loads ≤ 72 VA, make: cos = 0.3, break: cos = 0.3. AC-15 (1)



X: Current (A)

Y: Millions of operating cycles

(1) AC-15: switching electromagnetic loads ≥ 72 VA, make: cos = 0.7, break: cos = 0.4.