Product data sheet

Specifications





IEC contactor, TeSys Deca, nonreversing, 18A, 10HP at 480VAC, up to 100kA SCCR, 3 phase, 3 NO, 48VDC coil, open

LC1D18ED

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 170.00 USD

Main

Range Of Product	TeSys Deca
Product Or Component Type	Contactor
Device Short Name	LC1D
Contactor Application	Motor control Resistive load
Utilisation Category	AC-3 AC-1 AC-4 AC-3e
Poles Description	3P
[Ue] Rated Operational Voltage	Power circuit <= 690 V AC 25400 Hz Power circuit <= 300 V DC
[le] Rated Operational Current18 A (at <140 °F (60 °C)) at <= 440 V AC AC-3 for power circuit 32 A (at <140 °F (60 °C)) at <= 440 V AC AC-1 for power circuit 18 A (at <140 °F (60 °C)) at <= 440 V AC AC-3 for power circuit	
[Uc] Control Circuit Voltage	48 V DC

Complementary

Motor Power Kw	4 kW at 220230 V AC 50/60 Hz (AC-3)
	7.5 kW at 380400 V AC 50/60 Hz (AC-3)
	9 kW at 415440 V AC 50/60 Hz (AC-3)
	10 kW at 500 V AC 50/60 Hz (AC-3)
	10 kW at 660690 V AC 50/60 Hz (AC-3)
	4 kW at 400 V AC 50/60 Hz (AC-4)
	4 kW at 220230 V AC 50/60 Hz (AC-3e)
	7.5 kW at 380400 V AC 50/60 Hz (AC-3e)
	9 kW at 415440 V AC 50/60 Hz (AC-3e)
	10 kW at 500 V AC 50/60 Hz (AC-3e)
	10 kW at 660690 V AC 50/60 Hz (AC-3e)
Maximum Horse Power Rating	1 hp at 115 V AC 50/60 Hz for 1 phase motors
	3 hp at 230/240 V AC 50/60 Hz for 1 phase motors
	5 hp at 200/208 V AC 50/60 Hz for 3 phase motors
	5 hp at 230/240 V AC 50/60 Hz for 3 phase motors
	10 hp at 460/480 V AC 50/60 Hz for 3 phase motors
	15 hp at 575/600 V AC 50/60 Hz for 3 phase motors
Compatibility Code	LC1D
Pole Contact Composition	3 NO
Protective Cover	With
[Ith] Conventional Free Air	10 A (at 140 °F (60 °C)) for signalling circuit
Thermal Current	32 A (at 140 °F (60 °C)) for power circuit

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Irms Rated Making Capacity	140 A AC for signalling circuit conforming to IEC 60947-5-1
	250 A DC for signalling circuit conforming to IEC 60947-5-1
	300 A at 440 V for power circuit conforming to IEC 60947
Rated Breaking Capacity	300 A at 440 V for power circuit conforming to IEC 60947
[low] Dated Chart Time With stand	
[Icw] Rated Short-Time Withstand Current	145 A 104 °F (40 °C) - 10 s for power circuit
Guirent	240 A 104 °F (40 °C) - 1 s for power circuit
	40 A 104 °F (40 °C) - 10 min for power circuit
	84 A 104 °F (40 °C) - 1 min for power circuit
	100 A - 1 s for signalling circuit
	120 A - 500 ms for signalling circuit
	140 A - 100 ms for signalling circuit
Associated Fuse Rating	10 A gG for signalling circuit conforming to IEC 60947-5-1
	50 A gG at <= 690 V coordination type 1 for power circuit
	35 A gG at <= 690 V coordination type 2 for power circuit
Average Impedance	2.5 mOhm - Ith 32 A 50 Hz for power circuit
Power Dissipation Per Pole	2.5 W AC-1
	0.8 W AC-3
	0.8 W AC-3e
[Ui] Rated Insulation Voltage	Power circuit 690 V IEC 60947-4-1
	Power circuit 600 V CSA
	Power circuit 600 V UL
	Signalling circuit 690 V IEC 60947-1
	Signalling circuit 600 V CSA
	Signalling circuit 600 V UL
Overvoltage Category	
Pollution Degree	3
[Uimp] Rated Impulse Withstand Voltage	6 kV IEC 60947
	D40d - 4200002 avalage contestar with particul load EN/ICO 42040 4
Safety Reliability Level	B10d = 1369863 cycles contactor with nominal load EN/ISO 13849-1
	B10d = 20000000 cycles contactor with mechanical load EN/ISO 13849-1
Mechanical Durability	30 Mcycles
Electrical Durability	1.65 Mcycles 18 A AC-3 <= 440 V
,	1 Mcycles 32 A AC-1 <= 440 V
	1.65 Mcycles 18 A AC-3e <= 440 V
	·
Control Circuit Type	DC standard
Coil Technology	With integral suppression device
Control Circuit Voltage Limits	0.10.25 Uc -40158 °F (-4070 °C) drop-out DC
	0.71.25 Uc -40140 °F (-4060 °C) operational DC
	11.25 Uc 140158 °F (6070 °C) operational DC
Inrush Power In W	5.4 W 68 °F (20 °C))
Hold-In Power Consumption In W	5.4 W 68 °F (20 °C)
Operating Time	
Operating Time	63 ±15 % ms closing
	20 ±20 % ms opening
Time Constant	28 ms
Maximum Operating Rate	3600 cyc/h 140 °F (60 °C)

Connections - Terminals	Control circuit: screw clamp terminals 1 0.000.01 in ² (14 mm ²) - cable stiffness:
	flexible without cable end
	Control circuit: screw clamp terminals 2 0.000.01 in ² (14 mm ²) - cable stiffness: flexible without cable end
	Control circuit: screw clamp terminals 1 0.000.01 in ² (14 mm ²) - cable stiffness:
	flexible with cable end
	Control circuit: screw clamp terminals 2 0.000.00 in ² (12.5 mm ²) - cable stiffness:
	flexible with cable end
	Control circuit: screw clamp terminals 1 0.000.01 in ² (14 mm ²) - cable stiffness:
	solid without cable end
	Control circuit: screw clamp terminals 2 0.000.01 in ² (14 mm ²) - cable stiffness:
	solid without cable end
	Power circuit: screw clamp terminals 1 0.000.01 in ² (1.56 mm ²) - cable stiffness:
	flexible without cable end
	Power circuit: screw clamp terminals 2 0.000.01 in ² (1.56 mm ²) - cable stiffness:
	flexible without cable end
	Power circuit: screw clamp terminals 1 0.000.01 in ² (16 mm ²) - cable stiffness:
	flexible with cable end
	Power circuit: screw clamp terminals 2 0.000.01 in ² (14 mm ²) - cable stiffness:
	flexible with cable end
	Power circuit: screw clamp terminals 1 0.000.01 in ² (1.56 mm ²) - cable stiffness:
	solid without cable end
	Power circuit: screw clamp terminals 2 0.000.01 in ² (1.56 mm ²) - cable stiffness:
	solid without cable end
Tightening Torque	Power circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals flat Ø 6 mm
	Power circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals Philips No 2
	Control circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals flat Ø 6 mm
	Control circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals Philips No 2
	Control circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals pozidriv No 2
	Power circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals pozidriv No 2
Auxiliary Contact Composition	1 NO + 1 NC
Auxiliary Contacts Type	Mechanically linked 1 NO + 1 NC IEC 60947-5-1
	Mirror contact 1 NC IEC 60947-4-1
Signalling Circuit Frequency	25400 Hz
Minimum Switching Voltage	17 V for signalling circuit
Minimum Switching Current	5 mA for signalling circuit
Insulation Resistance	> 10 MOhm for signalling circuit
Non-Overlap Time	1.5 ms on de-energisation between NC and NO contact
·	1.5 ms on energisation between NC and NO contact
Mounting Support	Plate
	Rail
	i Nali

Environment

CSA C22.2 No 14 EN 60947-4-1	
EN 60947-5-1	
IEC 60947-4-1	
IEC 60947-5-1	
UL 508	
IEC 60335-1	
UL	
DNV	
RINA	
000	
GL	
GOST	
CSA	
LROS (Lloyds register of shipping)	
BV	
UKCA	
IP20 front face IEC 60529	
THIEC 60068-2-30	
IACS E10 exposure to damp heat IEC 60947-1 Annex Q category D exposure to damp heat	

Permissible Ambient Air Temperature Around The Device	-40140 °F (-4060 °C) e 140158 °F (6070 °C) with derating	
Operating Altitude	09842.52 ft (03000 m)	
Fire Resistance	1562 °F (850 °C) IEC 60695-2-1	
Flame Retardance	V1 conforming to UL 94	
Mechanical Robustness	Vibrations contactor open 2 Gn, 5300 Hz) Vibrations contactor closed 4 Gn, 5300 Hz) Shocks contactor open 10 Gn for 11 ms) Shocks contactor closed 15 Gn for 11 ms)	
Height	3.03 in (77 mm)	
Width	1.77 in (45 mm)	
Depth	3.74 in (95 mm)	
Net Weight	1.08 lb(US) (0.49 kg)	

Ordering and shipping details

Category	US10I1222355
Discount Schedule	0112
Gtin	3389110354812
Returnability	No
Country Of Origin	FR

Packing Units

in (5.000 cm)
in (5.000 cm)
in (5.000 cm)
in (9.200 cm)
in (11.200 cm)
1 oz (519.000 g)
in (15 cm)
1 in (30 cm)
5 in (40 cm)
6 lb(US) (8.33 kg)
2 in (45.000 cm)
2 in (60.000 cm)
0 in (80.000 cm)
21 lb(US) (151.14 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free
Rohs Exemption Information Yes
Pvc Free


Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov

Product data sheet

Dimensions Drawings

Dimensions



(1) Minimum electrical clearance

LC1	1	D09D18	D093D123	D099D129
b		77	99	80
	without cover or add-on blocks	93	93	93
C	with cover, without add-on blocks	95	95	95
c1	with LAD N or C (2 or 4 contacts)	126	126	126
c2	with LA6 DK10	138	138	138
~ 2	with LAD T, R, S	146	146	146
c3	with LAD T, R, S and sealing cover	150	150	150

Product data sheet

Connections and Schema

Wiring

