

Product data sheet

Specifications



contactor TeSys Deca - 3 poles - AC-3 440V 50 A - coil 48 V DC

LC1D50FD

⚠ Discontinued on: Jan 23, 2021

⚠ Discontinued

Main

Range	TeSys
Range Of Product	TeSys D
Product Or Component Type	Contactor
Device Short Name	LC1D
Contactor Application	Resistive load Motor control
Utilisation Category	AC-4 AC-2 AC-3 AC-2
Poles Description	3P
[Ue] Rated Operational Voltage	Power circuit <= 690 V AC 25...400 Hz
[Ie] Rated Operational Current	80 A (at <140 °F (60 °C)) at <= 440 V AC AC-1 for power circuit 50 A (at <140 °F (60 °C)) at <= 440 V AC AC-3 for power circuit
[Uc] Control Circuit Voltage	115 V AC 50 Hz

Complementary

Motor Power Kw	25 kW at 415 V AC 50 Hz 30 kW at 440 V AC 50 Hz 30 kW at 500 V AC 50 Hz 33 kW at 660...690 V AC 50 Hz 15 kW at 220...230 V AC 50 Hz 30 kW at 1000 V AC 50 Hz 22 kW at 380...400 V AC 50 Hz
Maximum Horse Power Rating	7.5 hp at 230/240 V AC 60 Hz for 1 phase motors 15 hp at 200/208 V AC 60 Hz for 3 phase motors 15 hp at 230/240 V AC 60 Hz for 3 phase motors 40 hp at 460/480 V AC 60 Hz for 3 phase motors 40 hp at 575/600 V AC 60 Hz for 3 phase motors 3 hp at 115 V AC 60 Hz for 1 phase motors
Compatibility Code	LC1D
Pole Contact Composition	3 NO
Protective Cover	With
[Ith] Conventional Free Air Thermal Current	80 A (at 140 °F (60 °C)) for power circuit 10 A (at 140 °F (60 °C)) for control circuit
Irms Rated Making Capacity	900 A at 440 V for power circuit conforming to IEC 60947 140 A AC for control circuit conforming to IEC 60947-5-1
Rated Breaking Capacity	900 A at 440 V for power circuit conforming to IEC 60947

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Associated Fuse Rating	100 A gG at ≤ 690 V coordination type 1 for power circuit 100 A gG at ≤ 690 V coordination type 2 for power circuit conforming to IEC 60947-5-1 10 A gG for control circuit conforming to IEC 60947-5-1
Power Dissipation Per Pole	9.6 W AC-1 3.7 W AC-3
[Ui] Rated Insulation Voltage	Control circuit 600 V UL Power circuit 600 V CSA Power circuit 600 V UL IEC 60947-1 Control circuit 690 V IEC 60947-1 Power circuit 690 V CSA IEC 60947-1 Control circuit 600 V CSA
Overvoltage Category	III
[Uimp] Rated Impulse Withstand Voltage	8 kV IEC 60947
Safety Reliability Level	B10d = 20000000 cycles contactor with mechanical load EN/ISO 13849-1 B10d = 1369863 cycles contactor with nominal load EN/ISO 13849-1
Mechanical Durability	6000000 cycles
Control Circuit Type	AC 50 Hz
Coil Technology	Without built-in bidirectional peak limiting diode suppressor
Control Circuit Voltage Limits	0.75...1.25 Uc -40...140 °F (-40...60 °C) operational DC 1...1.25 Uc 140...158 °F (60...70 °C) operational DC 50 Hz 0.8...1.1 Uc -40...131 °F (-40...55 °C) operational AC 50 Hz 0.3...0.6 Uc -40...158 °F (-40...70 °C) drop-out AC 50 Hz
Inrush Power In Va	140 VA cos phi 0.75 (at 68 °F (20 °C)) 160 VA cos phi 0.75 (at 68 °F (20 °C))
Hold-In Power Consumption In Va	13 VA 60 Hz cos phi 0.3 (at 68 °F (20 °C)) 15 VA 50 Hz cos phi 0.3 (at 68 °F (20 °C))
Heat Dissipation	4...5 W at 50/60 Hz for control circuit
Operating Time	50 ms closing 12...26 ms closing 4...19 ms opening
Maximum Operating Rate	3600 cyc/h 140 °F (60 °C)
Connections - Terminals	Control circuit: screw clamp terminals 2 0.00...0.01 in² (1...4 mm²) - cable stiffness: rigid without cable end Control circuit: screw clamp terminals 1 0.00...0.01 in² (1...4 mm²) - cable stiffness: flexible without cable end Control circuit: screw clamp terminals 2 0.00...0.01 in² (1...4 mm²) - cable stiffness: flexible without cable end Control circuit: screw clamp terminals 1 0.00...0.00 in² (1...2.5 mm²) - cable stiffness: flexible with cable end Control circuit: screw clamp terminals 2 0.00...0.00 in² (1...2.5 mm²) - cable stiffness: flexible with cable end Power circuit: screw terminals 1 0.00...0.04 in² (2.5...25 mm²) - cable stiffness: rigid Power circuit: screw terminals 2 0.00...0.02 in² (2.5...16 mm²) - cable stiffness: rigid without cable end Power circuit: screw terminals 1 0.00...0.04 in² (2.5...25 mm²) - cable stiffness: flexible without cable end Power circuit: screw terminals 2 0.00...0.02 in² (2.5...16 mm²) - cable stiffness: flexible without cable end Power circuit: screw terminals 1 0.00...0.04 in² (2.5...25 mm²) - cable stiffness: flexible with cable end Power circuit: screw terminals 2 0.00...0.02 in² (2.5...10 mm²) - cable stiffness: flexible with cable end Control circuit: screw clamp terminals 2 0.00...0.01 in² (1...4 mm²) - cable stiffness: rigid Control circuit: screw clamp terminals 1 0.00...0.01 in² (1...4 mm²) - cable stiffness: rigid
Tightening Torque	Control circuit 15.05 lbf.in (1.7 N.m) screw clamp terminal Philips No 2 Power circuit 44.25 lbf.in (5 N.m) screw terminal flat Ø 6 to Ø 8 mm Control circuit 15.05 lbf.in (1.7 N.m) screw clamp terminal pozidriv No 2 Control circuit 15.05 lbf.in (1.7 N.m) screw clamp terminal flat Ø 6 mm
Auxiliary Contact Composition	1 NO + 1 NC

Auxiliary Contacts Type	Mirror contact 1 NC IEC 60947-4-1 Mechanically linked 1 NO + 1 NC IEC 60947-5-1
Terminals Description Iso N°1	(13-14)NO
Minimum Switching Voltage	17 V for control circuit
Minimum Switching Current	5 mA for control circuit
Insulation Resistance	> 10 MOhm for control circuit
Non-Overlap Time	1.5 ms on energisation between NC and NO contacts 1.5 ms on de-energisation between NC and NO contacts
Mounting Support	Plate Rail

Environment

Standards	IEC 60947-5-1 EN 60947-4-1 CSA C22.2 No 14 EN 60947-5-1 UL 508 IEC 60947-4-1
Product Certifications	DNV UL CSA BV LROS (Lloyds register of shipping) CCC GOST RINA DNV
Ip Degree Of Protection	IP2X VDE 0106 IP2X IEC 60529
Climatic Withstand	IACS E10 exposure to damp heat
Permissible Ambient Air Temperature Around The Device	-76...176 °F (-60...80 °C) storage -40...140 °F (-40...60 °C) operation 140...158 °F (60...70 °C) with derating
Operating Altitude	0...9842.52 ft (0...3000 m)
Fire Resistance	1562 °F (850 °C) IEC 60695-2-1
Flame Retardance	V1 conforming to UL 94
Mechanical Robustness	Shocks contactor closed 15 gn) Vibrations contactor opened 2 Gn, 5...300 Hz) Vibrations contactor closed 4 Gn, 5...300 Hz) Shocks contactor opened 10 Gn)
Height	5.00 in (127 mm)
Width	2.95 in (75 mm)
Depth	4.69 in (119 mm)
Net Weight	3.09 lb(US) (1.4 kg)

Ordering and shipping details

Category	22358-CTR,TESYS D,OPEN,40-65A DC
Discount Schedule	I12
Gtin	3389110421293
Returnability	No
Country Of Origin	CZ

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes
✓	Pvc Free	

Certifications & Standards

Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	End of Life Information