Product data sheet

Specification





discrete IO extension module, Zelio Logic SR2 SR3, 14 IO, 12V DC

SR3XT141JD

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 140.00 USD

Main

Range Of Product	Zelio Logic
Product Or Component Type	Discrete I/O extension module

Complementary

Number Or Control Scheme Lines	120 ladder
Cycle Time	690 ms
Backup Time	10 years 77 °F (25 °C)
Clock Drift	12 min/year 32131 °F (055 °C)
Checks	Program memory on each power up
[Us] Rated Supply Voltage	12 V DC
Supply Voltage Limits	10.414.4 V
Reverse Polarity Protection	With
Discrete Input Number	8 IEC 61131-2 Type 1
Discrete Input Type	Resistive
Discrete Input Voltage	12 V DC
Discrete Input Current	4 mA
Counting Frequency	1 kHz discrete input
Voltage State 1 Guaranteed	>= 7 V IBIG used as discrete input circuit >= 5.6 V I1IA and IHIR discrete input circuit
Voltage State 0 Guaranteed	<= 3 V IBIG used as discrete input circuit <= 2.4 V I1IA and IHIR discrete input circuit
Current State 1 Guaranteed	>= 2 mA I1IA and IHIR discrete input circuit) >= 0.5 mA IBIG used as discrete input circuit)
Current State 0 Guaranteed	<= 0.2 mA IBIG used as discrete input circuit) <= 0.9 mA I1IA and IHIR discrete input circuit)
Input Compatibility	3-wire proximity sensors PNP discrete input
Input Impedance	14 kOhm IBIG used as discrete input circuit 2.7 kOhm I1IA and IHIR discrete input circuit
Number Of Outputs	6 relay
Output Voltage Limits	24250 V AC relay output) 530 V DC relay output)
Contacts Type And Composition	NO relay output

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Output Thermal Current	5 A for 2 outputs relay output 8 A for 4 outputs relay output	
Electrical Durability	AC-15 500000 cycles 230 V, 0.9 A relay output IEC 60947-5-1 AC-12 500000 cycles 230 V, 1.5 A relay output IEC 60947-5-1 DC-13 500000 cycles 24 V, 0.6 A relay output IEC 60947-5-1 DC-12 500000 cycles 24 V, 1.5 A relay output IEC 60947-5-1	
Switching Capacity In Ma	>= 10 mA 12 V relay output)	
Operating Rate In Hz	0.1 Hz at le)relay output 10 Hz no load)relay output	
Mechanical Durability	10000000 cycles relay output	
[Uimp] Rated Impulse Withstand Voltage	4 kV EN/IEC 60947-1 and EN/IEC 60664-1	
Response Time	10 ms from state 0 to state 1)relay output 5 ms from state 1 to state 0)relay output	
Connections - Terminals	Screw terminals, 1 x 0.251 x 2.5 mm² AWG 24AWG 14) flexible with cable end Screw terminals, 2 x 0.252 x 0.75 mm² AWG 24AWG 18) flexible with cable end Screw terminals, 1 x 0.21 x 2.5 mm² AWG 25AWG 14) semi-solid Screw terminals, 1 x 0.21 x 2.5 mm² AWG 25AWG 14) solid Screw terminals, 2 x 0.22 x 1.5 mm² AWG 24AWG 16) solid	
Tightening Torque	4.43 lbf.in (0.5 N.m)	
Overvoltage Category	III IEC 60664-1	
Net Weight	0.49 lb(US) (0.22 kg)	
Environment		
Product Certifications	GL UL GOST C-tick CSA	
Standards	IEC 61000-4-6 level 3 IEC 61000-4-3 IEC 61000-4-2 level 3 IEC 61000-4-4 level 3 IEC 60068-2-27 Ea IEC 61000-4-12 IEC 60068-2-6 Fc IEC 61000-4-11 IEC 61000-4-5	
Ip Degree Of Protection	IP20 IEC 60529 terminal block) IP40 IEC 60529 front panel)	
Environmental Characteristic	EMC directive IEC 61000-6-2 EMC directive IEC 61000-6-3 EMC directive IEC 61000-6-4 EMC directive IEC 61131-2 zone B Low voltage directive IEC 61131-2	
Disturbance Radiated/Conducted	Class B EN 55022-11 group 1	
Pollution Degree	2 IEC 61131-2	
Ambient Air Temperature For Operation	-4104 °F (-2040 °C) in non-ventilated enclosure IEC 60068-2-1 and IEC 60068-2-2 -4131 °F (-2055 °C) IEC 60068-2-1 and IEC 60068-2-2	
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)	
Operating Altitude	6561.68 ft (2000 m)	
Maximum Altitude Transport	10000.00 ft (3048 m)	
Relative Humidity	95 % without condensation or dripping water	

Ordering and shipping details

Category	US1000I22378
Discount Schedule	0001
Gtin	3389119203951
Returnability	Yes
Country Of Origin	US

Packing Units

_	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.68 in (6.800 cm)
Package 1 Width	3.54 in (9.000 cm)
Package 1 Length	3.94 in (10.000 cm)
Package 1 Weight	6.95 oz (197.000 g)
Unit Type Of Package 2	S03
Number Of Units In Package 2	30
Package 2 Height	11.81 in (30.000 cm)
Package 2 Width	11.81 in (30.000 cm)
Package 2 Length	15.75 in (40.000 cm)
Package 2 Weight	14.29 lb(US) (6.480 kg)

Contractual warranty

Warranty 18 months

Sustainability Green Premium"

Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Mercury Free	
	Rohs Exemption Information	Yes
②	Pvc Free	


Certifications & Standards

Reach Regulation	REACh Declaration	
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)	
China Rohs Regulation	China RoHS declaration	
Environmental Disclosure	Product Environmental Profile	
Weee	The product must be disposed on European Union markets following specific was collection and never end up in rubbish bins.	
Circularity Profile	End of Life Information	
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov	


Dimensions Drawings

I/O Extension Modules

Mounting on 35 mm/1.38 in. DIN Rail



Screw Fixing (Retractable Lugs)



SR3	a (mm/in.)	G (mm/in.)
XT61••	35 / 1.38	25 / 0.98
XT101••	72 / 2.83	60 / 2.36
XT141••	72 / 2.83	60 / 2.36


Connections and Schema

Connection of Smart Relays on DC Supply, with Analog I/O Extension Module

Connection Alternatives


0 - 10 V	0 - 20 mA	Pt100
2	0	0
1	1	0
0	2	0
1	0	1
0	1	1

Application Example with 1 x 0 - 10 V Input and 1 x Pt100 Input



(1) Screened cables, maximum length 10 m/32.80 ft.

Application Example with 1 x 0 - 20 mA Input and 1 x 0 - 10 V Input




(1) Screened cables, maximum length 10 m/32.80 ft.

Performance Curves

Compact and Modular Smart Relays

Electrical Durability of Relay Outputs

(in millions of operating cycles, conforming to IEC/EN 60947-5-1) DC-12 (1)




X: Current (A)

Y: Millions of operating cycles

(1) DC-12: control of resistive loads and of solid state loads isolated by opto-coupler, L/R ≤ 1 ms.

DC-13 (1)



X: Current (A)

Y: Millions of operating cycles

(1) DC-13: switching electromagnets, $L/R \le 2 \times (Ue \times Ie)$ in ms, Ue: rated operational voltage, Ie: rated operational current (with a protection diode on the load, DC-12 curves must be used with a coefficient of 0.9 applied to the number in millions of operating cycles).