# Product data sheet

Specifications





IEC contactor, TeSys Deca, nonreversing, 12A, 7.5HP at 480VAC, up to 100kA SCCR, 3 phase, 3 NO, 110VAC 50/60Hz coil, open

LC1D12F7

Product availability: Stock - Normally stocked in distribution facility

Price\*: 142.80 USD

#### Main

| Range Of Product               | TeSys Deca   |
|--------------------------------|--|
| Product Or Component Type      | Contactor  |
| Device Short Name              | LC1D   |
| Contactor Application          | Resistive load   |
|                                | Motor control  |
| Utilisation Category           | AC-3   |
|                                | AC-4   |
|                                | AC-1   |
|                                | AC-3e  |
| Poles Description              | 3P   |
| [Ue] Rated Operational Voltage | Power circuit <= 690 V AC 25400 Hz                               |
|                                | Power circuit <= 300 V DC  |
| [le] Rated Operational Current | 25 A (at <140 °F (60 °C)) at <= 440 V AC AC-1 for power circuit  |
|                                | 12 A (at <140 °F (60 °C)) at <= 440 V AC AC-3 for power circuit  |
|                                | 12 A (at <140 °F (60 °C)) at <= 440 V AC AC-3e for power circuit |
| [Uc] Control Circuit Voltage   | 110 V AC 50/60 Hz  |
|                                |  |

### Complementary

| Motor Power Kw             | 3 kW at 220230 V AC 50/60 Hz (AC-3)                |
|----------------------------|--|
|                            | 5.5 kW at 380400 V AC 50/60 Hz (AC-3)              |
|                            | 5.5 kW at 415440 V AC 50/60 Hz (AC-3)              |
|                            | 7.5 kW at 500 V AC 50/60 Hz (AC-3)                 |
|                            | 7.5 kW at 660690 V AC 50/60 Hz (AC-3)              |
|                            | 3.7 kW at 400 V AC 50/60 Hz (AC-4)                 |
|                            | 3 kW at 220230 V AC 50/60 Hz (AC-3e)               |
|                            | 5.5 kW at 380400 V AC 50/60 Hz (AC-3e)             |
|                            | 5.5 kW at 415440 V AC 50/60 Hz (AC-3e)             |
|                            | 7.5 kW at 500 V AC 50/60 Hz (AC-3e)                |
|                            | 7.5 kW at 660690 V AC 50/60 Hz (AC-3e)             |
| Maximum Horse Power Rating | 0.5 hp at 115 V AC 50/60 Hz for 1 phase motors     |
|                            | 2 hp at 230/240 V AC 50/60 Hz for 1 phase motors   |
|                            | 3 hp at 200/208 V AC 50/60 Hz for 3 phase motors   |
|                            | 3 hp at 230/240 V AC 50/60 Hz for 3 phase motors   |
|                            | 7.5 hp at 460/480 V AC 50/60 Hz for 3 phase motors |
|                            | 10 hp at 575/600 V AC 50/60 Hz for 3 phase motors  |
| Compatibility Code         | LC1D   |
| Pole Contact Composition   | 3 NO   |
| Protective Cover           | With   |
|                            |  |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

| [Ith] Conventional Free Air<br>Thermal Current | 25 A (at 140 °F (60 °C)) for power circuit<br>10 A (at 140 °F (60 °C)) for signalling circuit  |  |  |
|--|--|--|--|
| Irms Rated Making Capacity                     | 250 A at 440 V for power circuit conforming to IEC 60947<br>140 A AC for signalling circuit conforming to IEC 60947-5-1<br>250 A DC for signalling circuit conforming to IEC 60947-5-1   |  |  |
| Rated Breaking Capacity                        | 250 A at 440 V for power circuit conforming to IEC 60947   |  |  |
| [Icw] Rated Short-Time Withstand<br>Current    | 105 A 104 °F (40 °C) - 10 s for power circuit 210 A 104 °F (40 °C) - 1 s for power circuit 30 A 104 °F (40 °C) - 10 min for power circuit 61 A 104 °F (40 °C) - 1 min for power circuit 100 A - 1 s for signalling circuit 120 A - 500 ms for signalling circuit 140 A - 100 ms for signalling circuit |  |  |
| Associated Fuse Rating                         | 10 A gG for signalling circuit conforming to IEC 60947-5-1 40 A gG at <= 690 V coordination type 1 for power circuit 25 A gG at <= 690 V coordination type 2 for power circuit   |  |  |
| Average Impedance                              | 2.5 mOhm - Ith 25 A 50 Hz for power circuit  |  |  |
| Power Dissipation Per Pole                     | 0.36 W AC-3<br>1.56 W AC-1<br>0.36 W AC-3e   |  |  |
| [Ui] Rated Insulation Voltage                  | Power circuit 690 V IEC 60947-4-1 Power circuit 600 V CSA Power circuit 600 V UL Signalling circuit 690 V IEC 60947-1 Signalling circuit 600 V CSA Signalling circuit 600 V UL   |  |  |
| Overvoltage Category                           | III  |  |  |
| Pollution Degree                               | 3  |  |  |
| [Uimp] Rated Impulse Withstand Voltage         | 6 kV IEC 60947   |  |  |
| Safety Reliability Level                       | B10d = 1369863 cycles contactor with nominal load EN/ISO 13849-1<br>B10d = 20000000 cycles contactor with mechanical load EN/ISO 13849-1   |  |  |
| Mechanical Durability                          | 15 Mcycles   |  |  |
| Electrical Durability                          | 2 Mcycles 12 A AC-3 <= 440 V<br>0.8 Mcycles 25 A AC-1 <= 440 V<br>2 Mcycles 12 A AC-3e <= 440 V  |  |  |
| Control Circuit Type                           | AC 50/60 Hz standard   |  |  |
| Coil Technology                                | Without built-in suppressor module   |  |  |
| Control Circuit Voltage Limits                 | 0.30.6 Uc -40158 °F (-4070 °C) drop-out AC 50/60 Hz 0.81.1 Uc -40140 °F (-4060 °C) operational AC 50 Hz 0.851.1 Uc -40140 °F (-4060 °C) operational AC 60 Hz 11.1 Uc 140158 °F (6070 °C) operational AC 50/60 Hz   |  |  |
| Inrush Power In Va                             | 70 VA 60 Hz cos phi 0.75 (at 68 °F (20 °C))<br>70 VA 50 Hz cos phi 0.75 (at 68 °F (20 °C))   |  |  |
| Hold-In Power Consumption In Va                | 7.5 VA 60 Hz cos phi 0.3 (at 68 °F (20 °C))<br>7 VA 50 Hz cos phi 0.3 (at 68 °F (20 °C))   |  |  |
| Heat Dissipation                               | 23 W at 50/60 Hz   |  |  |
| Operating Time                                 | 1222 ms closing<br>419 ms opening  |  |  |
| Maximum Operating Rate                         | 3600 cyc/h 140 °F (60 °C)  |  |  |

| onnections - Terminals                  |  |
|---|--|
| Threetons - Terminais                   | Power circuit: screw clamp terminals 1 0.000.01 in² (14 mm²) - cable stiffness: flexible without cable end   |
|   | Power circuit: screw clamp terminals 2 0.000.01 in² (14 mm²) - cable stiffness: flexible without cable end   |
|   | Power circuit: screw clamp terminals 1 0.000.01 in² (14 mm²) - cable stiffness: flexible with cable end  |
|   | Power circuit: screw clamp terminals 2 0.000.00 in² (12.5 mm²) - cable stiffness:  |
|   | flexible with cable end Power circuit: screw clamp terminals 1 0.000.01 in² (14 mm²) - cable stiffness:  |
|   | solid without cable end Power circuit: screw clamp terminals 2 0.000.01 in² (14 mm²) - cable stiffness:  |
|   | solid without cable end Control circuit: screw clamp terminals 1 0.000.01 in² (14 mm²) - cable stiffness:  |
|   | flexible without cable end   |
|   | Control circuit: screw clamp terminals 2 0.000.01 in² (14 mm²) - cable stiffness: flexible without cable end   |
|   | Control circuit: screw clamp terminals 1 0.000.01 in² (14 mm²) - cable stiffness: flexible with cable end  |
|   | Control circuit: screw clamp terminals 2 0.000.00 in² (12.5 mm²) - cable stiffness: flexible with cable end  |
|   | Control circuit: screw clamp terminals 1 0.000.01 in² (14 mm²) - cable stiffness:  |
|   | solid without cable end Control circuit: screw clamp terminals 2 0.000.01 in² (14 mm²) - cable stiffness:  |
|   | solid without cable end  |
| ghtening Torque                         | Power circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals flat Ø 6 mm<br>Power circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals Philips No 2    |
|   | Control circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals flat Ø 6 mm   |
|   | Control circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals Philips No 2 Control circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals pozidriv No 2 |
|   | Power circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals pozidriv No 2   |
| ixiliary Contact Composition            | 1 NO + 1 NC  |
| ixiliary Contacts Type                  | Mechanically linked 1 NO + 1 NC IEC 60947-5-1<br>Mirror contact 1 NC IEC 60947-4-1   |
| gnalling Circuit Frequency              | 25400 Hz   |
| nimum Switching Voltage                 | 17 V for signalling circuit  |
| nimum Switching Current                 | 5 mA for signalling circuit  |
| sulation Resistance                     | > 10 MOhm for signalling circuit   |
| on-Overlap Time                         | 1.5 ms on de-energisation between NC and NO contact 1.5 ms on energisation between NC and NO contact   |
| ounting Support                         | Rail   |
|   | Plate  |
| nvironment                              |  |
| andards                                 | CSA C22.2 No 14  |
|   | EN 60947-4-1<br>EN 60947-5-1   |
|   | IEC 60947-4-1  |
|   | IEC 60947-5-1  |
|   | IEC 60335-1  |
| oduct Certifications                    | ccc  |
|   | BV<br>CSA  |
|   | GL   |
|   | UL   |
|   | RINA<br>GOST   |
|   | LROS (Lloyds register of shipping)   |
|   | DNV<br>UKCA  |
|   |  |
| Degree Of Protection                    | IP20 front face IEC 60529  |
| Degree Of Protection otective Treatment | IP20 front face IEC 60529  THIEC 60068-2-30  |
|   |  |
| oduct Certifications                    | CCC BV CSA GL UL RINA GOST LROS (Lloyds register of shipping)  |

| Permissible Ambient Air<br>Temperature Around The Device | -40140 °F (-4060 °C)  ce 140158 °F (6070 °C) with derating  |  |
|--|---|--|
| Operating Altitude                                       | 09842.52 ft (03000 m)   |  |
| Fire Resistance  | 1562 °F (850 °C) IEC 60695-2-1  |  |
| Flame Retardance   | V1 conforming to UL 94  |  |
| Mechanical Robustness                                    | Vibrations contactor open 2 Gn, 5300 Hz) Vibrations contactor closed 4 Gn, 5300 Hz) Shocks contactor open 10 Gn for 11 ms) Shocks contactor closed 15 Gn for 11 ms) |  |
| Height   | 3.03 in (77 mm)   |  |
| Width  | 1.77 in (45 mm)   |  |
| Depth  | 3.39 in (86 mm)   |  |
| Net Weight   | 0.72 lb(US) (0.325 kg)  |  |

# Ordering and shipping details

| Category          | US10l1222354  |
|-------------------|---------------|
| Discount Schedule | 0112          |
| Gtin              | 3389110349221 |
| Returnability     | Yes           |
| Country Of Origin | ID            |

## **Packing Units**

| Unit Type Of Package 1       | PCE                       |
|------------------------------|---------------------------|
| Number Of Units In Package 1 | 1                         |
| Package 1 Height             | 2.09 in (5.3 cm)          |
| Package 1 Width              | 3.70 in (9.4 cm)          |
| Package 1 Length             | 4.49 in (11.4 cm)         |
| Package 1 Weight             | 12.45 oz (353 g)          |
| Unit Type Of Package 2       | S02                       |
| Number Of Units In Package 2 | 20                        |
| Package 2 Height             | 5.91 in (15 cm)           |
| Package 2 Width              | 11.81 in (30 cm)          |
| Package 2 Length             | 15.75 in (40 cm)          |
| Package 2 Weight             | 16.61 lb(US) (7.535 kg)   |
| Unit Type Of Package 3       | P06                       |
| Number Of Units In Package 3 | 320                       |
| Package 3 Height             | 31.50 in (80 cm)          |
| Package 3 Width              | 31.50 in (80 cm)          |
| Package 3 Length             | 23.62 in (60 cm)          |
| Package 3 Weight             | 285.23 lb(US) (129.38 kg) |

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

| <b>Ø</b> | Reach Free Of Svhc             |
|----------|--------------------------------|
| <b>Ø</b> | Toxic Heavy Metal Free         |
| <b>Ø</b> | Mercury Free                   |
| <b>Ø</b> | Rohs Exemption Information Yes |
| <b>⊘</b> | Pvc Free                       |


#### **Certifications & Standards**

| Reach Regulation          | REACh Declaration   |  |  |  |
|---------------------------|---|--|--|--|
| Eu Rohs Directive         | Compliant EU RoHS Declaration   |  |  |  |
| China Rohs Regulation     | China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)   |  |  |  |
| Environmental Disclosure  | Product Environmental Profile   |  |  |  |
| Weee                      | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.  |  |  |  |
| Circularity Profile       | End of Life Information   |  |  |  |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov |  |  |  |
|                           |   |  |  |  |

## LC1D12F7

### **Dimensions Drawings**

#### **Dimensions**



- (1) Including LAD 4BB
- (2) Minimum electrical clearance

| LC1 |                                    | D09D18             | D093D123           | D099D129             |
|-----|------------------------------------|--------------------|--------------------|----------------------|
| b   | without add-on blocks              | 77                 | 99                 | 80                   |
|     | with LAD 4BB                       | 94                 | 107                | 95.5                 |
|     | with LA4 D●2                       | 110 <sup>(1)</sup> | 123 <sup>(1)</sup> | <sub>111.5</sub> (1) |
| b1  | with LA4 DF, DT                    | 119 <sup>(1)</sup> | 132 <sup>(1)</sup> | 120.5 <sup>(1)</sup> |
|     | with LA4 DW, DL                    | <sub>126</sub> (1) | 139 <sup>(1)</sup> | <sub>127.5</sub> (1) |
| С   | without cover or add-on blocks     | 84                 | 84                 | 84                   |
|     | with cover, without add-on blocks  | 86                 | 86                 | 86                   |
| с1  | with LAD N or C (2 or 4 contacts)  | 117                | 117                | 117                  |
| c2  | with LA6 DK10, LAD 6K10            | 129                | 129                | 129                  |
| с3  | with LAD T, R, S                   | 137                | 137                | 137                  |
|     | with LAD T, R, S and sealing cover | 141                | 141                | 141                  |
| (1) | Including LAD 4BB.                 |                    |                    |                      |

Connections and Schema

Wiring

